

ANDOR
an Oxford Instruments company

System Performance Booklet



System Overview

Description		Model					Serial Number		
CCD Head	✓	D	U	9	34P	-	BR-DD-9XT	CCD-20476	
TE Cooler performance (✓)						High		Ultra-high	✓
Accessories		Power Supply Unit (PS -24)					PS -25		
		--					✓		
		SO-		LM-		MFL-			
Serial/Batch Number									
Other									

☒ Sensor types are defined in Table 1 using the last two letters in box Model Number.

CCD Details

Manufacturer / Model No.		Pixels	Serial Number
E2V	CCD47-10	1024x1024, 13µm x 13µm	12262-17-02
E2V	CCD57-10	512x512, (FT), 13µm x 13µm	
E2V	CCD77-00	512x512, 24µm x 24µm	

Special Feature	(✓)	(✓)
NIMO	✓	Custom Mounting Flange
Fringe Suppression		Custom Cables
Shielded Anti-Blooming		


Window Variant	(✓)	(✓)
VUV-UV Parallel		NUV-Enhanced Parallel
Broadband VUV-NIR Wedged		Broadband VUV-NIR Parallel
Broadband VIS-NIR Wedged		Broadband VIS-NIR Parallel
VIS-NIR Enhanced Wedged		Bose-Einstein 780nm Wedged
None		Other

Summary of System Test Data

Readout Noise ♦1 and Base Mean Level

A/D Rate (MHz All 16 bit)	Preamp setting	CCD	Single Pixel	Full Vert Bin	Base Level ♦2
		Sensitivity ♦3 eles per A/D count	Noise electrons	Noise electrons	(Counts)
5	x1	7.0	36.1	34.6	951
5	x2	2.9	17.5	16.3	1421
5	x4	1.7	14.7	13.7	2597
3	x1	6.2	20.8	19.8	1071
3	x2	3.0	12.8	12.6	2001
3	x4	1.4	10.1	9.8	3418
1	x1	5.4	11.2	10.8	903
1	x2	2.8	8.2	8.0	1824
1	x4	1.3	6.7	6.4	3719
0.05	x1	5.4	5.0	5.0	549
0.05	x2	3.0	3.8	3.8	1451
0.05	x4	1.4	3.7	3.7	3308
Saturation Signal per pixel			129259	Electrons/pixel	

CCD Dark Current



Minimum Dark Current Achievable ♦4	0.000423	electrons/pixel/sec		
@ Sensor Temperature of ♦5	-91.578	°C	16	°C cooling Water
		With PS-25		
CCD Dark Current Uniformity better than ♦6	0.4298	electrons/pixel/sec		

Linearity and Uniformity

Linearity better than ♦7	1	% over 16 bits
Response Uniformity better than ♦8	1.7	%

Response Defects

White/Black Spots ♦9				(X, Y)
Centroid		Number of Pixels	Centroid	
(<input type="text" value="X"/> , <input type="text" value="X"/>)		<input type="text" value="X"/>	(<input type="text"/> , <input type="text"/>)	
(<input type="text"/> , <input type="text"/>)			(<input type="text"/> , <input type="text"/>)	
(<input type="text"/> , <input type="text"/>)			(<input type="text"/> , <input type="text"/>)	
(<input type="text"/> , <input type="text"/>)			(<input type="text"/> , <input type="text"/>)	
(<input type="text"/> , <input type="text"/>)			(<input type="text"/> , <input type="text"/>)	
(<input type="text"/> , <input type="text"/>)			(<input type="text"/> , <input type="text"/>)	
White/Black Columns ♦10			Column numbers indicated	<input type="text" value="X"/> <input type="text" value="X"/> <input type="text" value="X"/> <input type="text" value="X"/>
Trap ♦11		(X, Y)	(<input type="text" value="X"/> , <input type="text" value="X"/>)	

Dark Current Defects

Hot Spots ♦12				(X, Y)
Centroid		Number of Pixels	Centroid	
(<input type="text" value="X"/> , <input type="text" value="X"/>)		<input type="text" value="X"/>	(<input type="text"/> , <input type="text"/>)	
(<input type="text" value="X"/> , <input type="text" value="X"/>)		<input type="text" value="X"/>	(<input type="text"/> , <input type="text"/>)	
(<input type="text"/> , <input type="text"/>)			(<input type="text"/> , <input type="text"/>)	
(<input type="text"/> , <input type="text"/>)			(<input type="text"/> , <input type="text"/>)	
(<input type="text"/> , <input type="text"/>)			(<input type="text"/> , <input type="text"/>)	
(<input type="text"/> , <input type="text"/>)			(<input type="text"/> , <input type="text"/>)	
Hot Columns ♦13			Column numbers indicated	<input type="text" value="X"/> <input type="text" value="X"/>

Test Conditions

Readout Noise tested at	-80	°C with	16	°C water
Base Mean Level measured at	-80	°C with	16	°C water
Dark Current Uniformity tested at	-65	°C with	16	°C water
Blemishes tested at	-65	°C with	16	°C water

Custom Testing

System Passed for Shipping

Signed

Date

K.MCDOWELL

20TH MARCH 2017

Hardware	HEADBOARD	FPGA
Version #	AF	20.24
Shipping	SOLIS	SDK
Software	--	--
Version #		
Testing	SOLIS	SDK
Software	4.30.30002.0	2.102.30002.0
Version #		

▽ **Table 1; Key code to define the meanings of the last two letters in the Model Number**

Sensor Options			
OE	Open electrode	BU2	Back Illuminated (BI) + 250nm UV optimised
FI	Front illuminated (FI)	BU	BI + UV (350nm) optimised
UV	FI+UV coating	BV	BI + VIS (550nm) optimised
FO	FI + Fibre optic	BR-DD	BI + NIR +deepdepletion
FI-DD	FI + deep depletion	BN	BI with no AR coating

Performance Notes

- ◆1 Readout Noise is measured for both single pixel (SP) and fully vertically binned (FVB) with the CCD in darkness at temperature indicated and minimum exposure time. Noise values will change with pre-amplifier gain selection [PAG].
- ◆2 Average electronic DC offset for CCD in darkness at temperature indicated and minimum exposure time under dark conditions measured by single pixel (SP) for imaging systems and by (FVB) for spectroscopic systems.
- ◆3 Sensitivity is calculated in photoelectrons per A/D count from measurements of the Photon Transfer Curve.
- ◆4 Dark current falls exponentially with temperature. However, for a given temperature the actual dark current can vary by more than an order of magnitude from device to device. The devices are specified in terms of minimum dark current achievable rather than minimum temperature.
- ◆5 Minimum temperature achieved for thermoelectric (TE) cooler set to maximum value with water cooling
- ◆6 RMS (root mean square) deviation of dark current for fully binned operation for spectroscopic cameras, or full resolution image for imaging cameras, under dark conditions at temperature indicated (pixel/column defects not included). This variation is mainly cosmetic since it is fully subtractable without significant loss of performance.
- ◆7 Linearity is measured from a plot of Counts vs. Signal over the 16 bit dynamic range. Linearity is expressed as a %age deviation from a straight line fit. This quantity is not measured on individual systems.
- ◆8 RMS (root mean square) deviation from the average response of the CCD in full resolution image for imaging cameras, illuminated with uniform white light (defects not included).
- ◆9 White/black pixels have signals >25% above/below the average (25% contrast) with uniform illumination across the sensor.
- ◆10 A black column is defined as having ≥ 10 black pixels for imaging cameras.
- ◆11 Pixels which absorb charge as it is clocked through the defective area. When the light source is switched off, the signal from the trap appears to drop off more slowly than the signal from the surrounding pixels.
- ◆12 Hot spots are counted if they exhibit >50 times the maximum specified dark current at the test temperature indicated.
- ◆13 A column is considered defective if >10 pixels are affected, or if the column exhibits >2 times the maximum specified dark current at the test temperature indicated.

ENI 00448 iKon-M Photo Packing List

Sales order # 524844

Date. 21/3/17

Packer. Paul

Power supply PS-25

Yes



No



iKon M

Ser No. CCD-20476

USB cable

Yes



No



3mm, 7/64,
3/32 Allen key

Yes



No



Mains cable

Yes



No



2.0m SMB/BNC cable

Yes



No



Software

SDK: ✗

SOLIS: ✗

User Manual

Yes



No



ANDOR
an Oxford Instruments company

Product Manuals
Version: 15.09

© Andor Technology Ltd. All rights reserved.

Andor Technology
425 Sullivan Avenue
Suite #3
South Windsor, CT 06074, USA
Tel (860) 290-9211

PACKING LIST

SJSU RES FOUND/MARK YARBROUGH
MOSS LANDING MARINE LABS
965 N NIMITZ HIGHWAY
HONULULU, HI 96817
UNITED STATES

Shipping Ref	Customer	Date	Customer Ref.	Carrier	Control Code	LOC
524844	SANJOSEU	21/03/17	F017849		EU-GEA	n

Model Number	Description	Serial No.	Qty.	Packed
10 DU934P-BR-DD-9XT	1024x1024,13um,BR-DD,5MHz,-100C	CCD-20476	1	
10 WN35FS(BB-VS-NR)U	*35,broadband VIS-NIR,no W		1	

TERMS: NET 30

END USER: MARK YARBROUGH

ANDOR CONTACT: ANIKA HALL